


ONYX COPILOT

Flexible LED reading light




20 lm

Pleasantly warm and glare-free light



37 cm

370 mm neck length powered via cigarette lighter or with a plastic base for fixed connection



12 V + 24 V

The stylish light is suitable for both passenger cars (12 volt) and trucks (24 volt)



Precisely illuminating vehicle interiors

With its elegant and dynamic design, the ONYX COPILOT LED reading light achieves seamless integration into vehicle interiors. With its high flexibility, the reading light has a wide range of options for illuminating specific areas of the vehicle interior. The neck of the light is made of matt black silicon rubber and can be individually adjusted. The LED lifetime of ONYX COPILOT is extremely long: up to 20,000 hours! The Luminaire can be switched on/off and remain connected permanently. OSRAM provides a 2 year guarantee for this stylish light.

Product family datasheet

Technical data

Environmental & Regulatory Information Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)				
Product description	Candidate list substance 1	CAS No. of substance 1	Safe use instruction	Declaration no. in SCIP database
ONYX COPILOT M+7	Lead	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	a8fbe42d-eed7-4920-85e5-453aad7ab825
ONYX COPILOT	Lead	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	abeee974-0574-456e-82ec-afd9be936f89

Product description	Primary article identifier
ONYX COPILOT M+7	
ONYX COPILOT	4052899414938

Download Data

File	
	User instruction GPRS_Safety symbols instructions
	User instruction UI LED ONYX COPILOT L
	User instruction LED ONYX COPILOT L

References / Links

Guarantee terms are available at www.osram.com/am-guarantee

Application advice

For more detailed application information and graphics please see product datasheet.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.